

# Auto Refracto - Keratometer

# URK-800F



**C E** 2195



Brilliantly Conceived & Beautifully Crafted

# URK-800F

Auto Refracto - Keratometer

# More Wide LCD & More Intuitive User Interface.

You can check how much crystalline lens are blurred by cataract and cornea is injured. At the same time, Save 2 cuts for each eye (Max.4 cuts for one patient), Furthermore can compare the captured data.

## **Enhanced Measuring Speed**

The image chips is specially designed have made REF measuring speed faster than before. In the past, it need to wait until the fogging is over but now it could measure even the fogging is not yet over, and it can get a more accurate measurment data.

#### Convenient Lock Knob

The user can lock the equipment just by pushing and pulling the knob.





#### Automatic Cutting Printer

The printing paper with data is cut automatically with high speed.

# Measure Iris and Pupils Diameters

By image capturing function, user can check Iris & Pupil diameters with ease. Therefore, accuracy of opotmetry will be reinforced.

## 20° Tilted Monitor Display

LCD Monitors are designed to view till 20 degrees so that the user could operate the machine more conveniently.



#### 7 Inch color TFT LCD

User can enjoy more clear images with specially designed image chips and 7 inch color TFT LCD.



# **Convenient User Menu Setting**

The menu screen are designed by each page so that it may alter set-up easily and faster.



# Consumer-Oriented Designs

Specially designed chips back up more clear graphic user interface, noticeable icons.



# Electric Powered Chinrest

User can move new chin rest just by pressing the button and new designed sensors make you avoid wrong operation in advance.



## **SPECIFICATIONS**

#### Measurement Mode

R/K mode	Successive Refractometry & Keratometry
Ref mode	Refractometry
Ker mode	Keratometry
CLBC mode	Contact lens base curve measurement

## Refractometry

Vertex Distance (VD)	0.0, 10.0, 12.0, 13.5, 15.0 mm
SPH	-25.00 ~ +22.00 D (0.12 D / 0.25 D)
CYL	0.00 ~ +/-10.00D
AXIS	1 ~ 180°
Cylinder Form	-, +, +/-
Pupil Distance	10 ~ 85 mm
Minimum Pupil Diameter	Ø 2.0

# Keratometry

	-
Radius of Curvature	5.0 ~ 10.2 mm
Corneal Power	33 ~ 67.50 D
Corneal Astigmatism	0.00 ~ -15.00 D (0.12 / 0.25 D)
AXIS	1 ~ 180°
Corneal Diameter	2.0 ~ 12.00 mm

#### Others

Printer	Thermal / Auto cutting
Power Saving	Nominate by 3, 5, 10 minutes
Display	7 Inch TFT LCD colored Monitor
Power Supply	AC 100 ~ 240V, 50 / 60Hz / 90W
Dimension / Weight	275(W) X 525(D) X 440(H), 20Kg
Chinrest Movement	Max., 65mm, Motorized operating
Data Output	RS-232 Interface, Video Output

Designs and details can be changed without prior notice for its improvements.

# **UNICOS**

UNICOS Co., Ltd.

282–30, Munji-ro, Yuseong-gu, Daejeon, Republic of Korea (ZIP CODE) 34050 Tel +82-42-825-8045 Fax +82-42-825-8041

E-mail: marketing1@e-unicos.com

## Distributed by



15 Avenida A 21-13, Zona 13 ; Ciudad de Guatemala; Guatemala. PBX: +502 2306-9096

Página Web: www.corpoadvance.com WhatsApp Business:+502 3203-3501